



# HYDRAULIC BRAKES MOTOR-BRAKES & VALVE BLOCKS



**SAE version**

# ACCESSORIES and MOTOR-BRAKES

## CONTENTS

	Page
● Hydraulic Disc Brake for MLHP, MLHR and MLHS type LB/288 .....	3
● Hydraulic Disc Brake for MLHSS type LBS/289(290) and MLHSV type LBV/289(290) .....	6
● Hydraulic Disc Brake for MLHTS type LBS/314(315) and MLHTV type LBV/314(315) .....	10
● Hydraulic Disc Brake type B...R .....	17
● Hydraulic Disc Brake type B...T .....	18
● Hydraulic Motor-brakes type B/HR .....	19
● Hydraulic Motor-Brakes type RWB .....	23
● Hydraulic Motor-brakes type SW .....	28
● Hydraulic Motor-brakes type TW .....	31
● Overcenter Valves with Brake Control .....	34
● Switch Valves .....	42
● Crossover Relief Valves .....	44
● Cross Port Relief Valves .....	52
● Motor-Brakes Special Features .....	55
● Application Calculation .....	56

"M+S HYDRAULIC" can accept no responsibility for possible errors in catalogues, brochures and other printed material.

"M+S HYDRAULIC" reserves the right to alter its products without notice. This also applies to products already on order provided that such alterations can be made without subsequential changes being necessary in specifications already agreed.

# HYDRAULIC DISC BRAKES LB, LBS, LBV - Wet



## APPLICATION

- » Heavy Duty machinery
- » Wheel drives
- » Material handling
- » Mining
- » Agricultural machines
- » Conveyors
- » Door openers and swing drives etc.




## GENERAL

<b>Fluid type</b>	Mineral based- HLP(DIN 51524) or HM(ISO 6743/4)
<b>Temperature range, °F [°C]</b>	-40÷284 [-430÷140]
<b>Viscosity range, SUS [mm<sup>2</sup>/s]</b>	98÷347 [20÷75]
<b>Filtration</b>	ISO code 20/16 (nominal filtration of 25 microns)
<b>Maintenance</b>	Changed after the first 50-100 h, then after every 500-1500 h.


## CONTENTS

Hydraulic Disc Brake for MLHP, MLHR and MLHS Motors type LB/288 ...	4÷5
Hydraulic Disc Brake for MLHSS type LBS/289 .....	6
Hydraulic Disc Brake for MLHSV type LBV/289 .....	7
Hydraulic Disc Brake for MLHSS type LBS/290 .....	8
Hydraulic Disc Brake for MLHSV type LBV/290 .....	9
Output Shafts Extensions for LBS(LBV)/289, 290 .....	10
Load curve for LBS(LBV)/289, 290 .....	10
Order code for LB.../288... .....	11
Hydraulic Disc Brake for MLHTS type LBS/314 .....	12
Hydraulic Disc Brake for MLHTS type LBS/315 .....	13
Load curve for LBS(LBV)/314, 315 .....	13
Hydraulic Disc Brake for MLHTV type LBV/314, 315 .....	14
Output Shafts Extensions for LBS(LBV)/314, 315 .....	15
Internal Spline Data .....	15
Order Code .....	16


**LB, LBS**



**LBV**



**HYDRAULIC DISC BRAKE TYPE LB../288...**  
**FOR FLANGE ATTACHMENT TO MLHP, MLHR AND MLHS HYDRAULIC MOTORS**



**SPECIFICATION DATA**

Description LB../288...	7	14	21	32	43	63
** Min. Static Torque, lb-in [daNm]	531-708 [6-8]	1150-1327 [13-15]	1770-1947 [20-22]	2743-3009 [31-34]	3628-3982 [41-45]	5399-5665 [61-64]
Opening Pressure, PSI [bar]	min 58-116 [4-8]	130-232 [9-16]	174-188 [12-13]	260-290 [18-20]	348-377 [24-26]	550-565 [38-39]
	max	4350 [300]				
Min. oil quantity for brake releasing, in <sup>3</sup> [cm <sup>3</sup> ]	.427 - .488 [7 - 8]					
Oil volume, in <sup>3</sup> [cm <sup>3</sup> ]	3.5 - 7.35 [50 - 120]					
Max. Pressure in drain space, PSI [bar]	7.25 [0,5]					
Weight lb [kg]	19.8 [9]					


\*\*Static torque is obtained at working pressure - 0 PSI [0 bar].




**INPUT SHAFT HOLES for LB.../288**

**OUTPUT SHAFT EXTENSIONS for LB.../288**


**C**



**G**




**S**




**C**

1"[25,4] straight, Parallel key 1/4"x1/4"x1/4" BS 46  
Max. Torque 3900 lb-in [44 daNm]




**G**

1"[25,4], SAE 6B Splined  
Max. Torque 3900 lb-in [44 daNm]





**S**

13T Splined 7/8"[22,22], ANS B92.1-1976  
Max. Torque 3200 lb-in [36 daNm]




**LOAD CURVE**





▽ - Disc Brake Mounting Surface



**INPUT FACE**



**HYDRAULIC DISC BRAKE TYPE LBS.../289...  
FOR FLANGE ATTACHMENT TO MLHSS HYDRAULIC MOTORS**




**OUTPUT SHAFT**  
see page 10


- C** : Brake release Port- 7/16 - 20UNF, deep .47 [12]
- D** : Drainage tap- 9/16 - 18UNF, deep .51 [13]
- \* - For Output Shaft Version T
- \*\* - For Output Shaft Version S



**INPUT SHAFT**  
see page 15



**OUTPUT SHAFT**  
see page 10



▽ - Place for attachment  
(tightening torque for screws 4x 1/2-13UNC, 1 1/4 in [31,8 mm] long  
ANSI B 18.3-76: 620 lb-in [7 daNm])


▽▽ - Place for attachment

**SPECIFICATION DATA**

Description LBS(LBV)../289(290)	21	32	43	63
* Min. Static Torque lb-in [daNm]	1770-1947[20-22]	2743-3009[31-34]	3628-3982[41-45]	5399-5665[61-64]
Opening Pressure	min	174-188 [12-13]	260-290 [18-20]	348-377 [24-26]
	max	4350 [300]		
Min. oil quantity for brake releasing	.427- .488 [7- 8]			
Oil volume	3.05-7.32 [50-120]			
Max. Pressure in in drain space	72[5]			
Weight for .../289 for .../290	22 [10] 24.2 [11]			

\*Static torque is obtained at working pressure - 0 PSI [0 bar].


**HYDRAULIC DISC BRAKE TYPE LBV.../289...  
FOR FLANGE ATTACHMENT TO MLHSV HYDRAULIC MOTORS**



OUTPUT SHAFT  
see page 10

**OUTPUT FACE**

**A SAE A Mount**




INPUT SHAFT  
see page 15

**C** : Brake release Port- 7/16 - 20UNF, deep .47 [12]  
**D,T** : Drainage tap- 9/16 - 18UNF, deep .51 [13]




▽ - Place for attachment  
(tightening torque for screws 4xM10 DIN 912 - 440 lb-in [5 daNm])

▽▽ - Place for attachment



OUTPUT SHAFT  
see page 10


**B SAE B Mount**




\* - For Output Shaft Version T  
\*\* - For Output Shaft Version S

**INPUT FACE  
For Versions 289 and 290**

**TYPE LBS.../...**




**TYPE LBV.../...**



**HYDRAULIC DISC BRAKE TYPE LBS.../290...  
FOR FLANGE ATTACHMENT TO MLHSS HYDRAULIC MOTORS**

INPUT SHAFT  
see page 15




OUTPUT SHAFT  
see page 10

**OUTPUT FACE**


**E Wheel Mount**

.531 [13,5] Dia. Mounting Hole  
on 5.811 [147,6] Dia. B. C.  
(4 places)




**R Wheel Mount**

INPUT SHAFT  
see page 15




OUTPUT SHAFT  
see page 10




**W SAE C Wheel Mount**

INPUT SHAFT  
see page 15



OUTPUT SHAFT  
see page 10



**C** : Brake release Port- 7/16 - 20UNF, deep .47 [12]  
**D,T** : Drainage tap- 9/16 - 18UNF, deep .51 [13]




▽ - Place for attachment  
(tightening torque for screws 4x 1/2-13UNC, 1 1/4 in [31,8 mm] long  
ANSI B 18.3-76: 620 lb-in [7 daNm])

▽▽ - Place for attachment



**HYDRAULIC DISC BRAKE TYPE LBV.../290...  
FOR FLANGE ATTACHMENT TO MLHSV HYDRAULIC MOTORS**


INPUT SHAFT  
see page 15




OUTPUT SHAFT  
see page 10

**OUTPUT FACE**

**E Wheel Mount**




INPUT SHAFT  
see page 15




OUTPUT SHAFT  
see page 10

**R Wheel Mount**




INPUT SHAFT  
see page 15



OUTPUT SHAFT  
see page 10


**W SAE C Wheel Mount**



**C** : Brake release Port- 7/16 - 20UNF, deep .47 [12]  
**D,T** : Drainage tap- 9/16 - 18UNF, deep .51 [13]

▽ - Place for attachment  
(tightening torque for screws 4xM10 DIN 912 - 440 lb-in [5 daNm])


▽▽ - Place for attachment



**OUTPUT SHAFT EXTENSIONS for LB.../289, 290**


**C**

1 1/4" [31,75] straight, Parallel key 5/16" x 5/16" x 1 1/4" BS 46  
Max. Torque 6815 lb-in [77 daNm]




**G**

14T Splined, 1 1/4" [31,75], ANS B92.1-1976  
Max. Torque 6815 lb-in [77 daNm]




**T**

1 1/4" [31,75], SAE J501 Tapered  
Parallel key 5/16" x 5/16" x 1" BS46  
Max. Torque 6815 lb-in [77 daNm]



**S**

1" [25,4], SAE 6B Splined  
Max. Torque 3900 lb-in [44 daNm]




**LOAD CURVE**


The curve applies to a B10 bearing life of 3000 hours at 200 RPM.

- 1: Pa < 350 daN [787 lbs]
- 2: Pa = 500 daN [1125 lbs]

**LBS(V).../289**



**LBS(V).../290**



**ORDER CODE for LB/288**

	1	2	3	4	5	6
<b>L B</b>		/ 2 8 8	-			

**Pos.1 - Output Face**

- A** - SAE A Mount
- B** - SAE B Mount

**Pos.2 - Input Shaft Holes** [see slots of page 5 left]

**C, G, S**

**Pos.3 - Static Torque Code** [see Specification Data]

7, 14, 21, 32, 43

**Pos.4 - Output Shaft Extensions\*** [see page 5]

- C** - 1"[25,4] straight, Parallel key
- G** - 1"[25,4] SAE 6B Splined
- S** - 7/8"[22,2] 13T Splined

**Pos.5 - Option [Paint]\*\***

- omit - no Paint
- P** - Painted
- PC** - Corrosion Protected Paint

**Pos.6 - Design Series**

- omit - Factory specified

Notes: \* For Max. Torque values see data on page 5.

The permissible output torque for shafts must not be exceeded!

\*\* Color at customer's request.

**ORDER CODE for LBS(LBV)/289 and 290**

	1	2	3	4	5	6	7
<b>L B</b>		/	-				

**Pos.1 - Type**

- S** - Disc Brake for short motor **S**- MLHSS
- V** - Disc Brake for very short motor **V**- MLHSV

**Pos.2 - Output Face**

- A** - SAE A Mount
- B** - SAE B Mount
- E** - Wheel Mount
- R** - Wheel Mount
- W** - SAE C Wheel Mount

**Pos.3 - Design Code**

- 289** - for MLHSS and MLHSV Motors
- 290** - for MLHSS and MLHSV Motors [Wheel Mounting Motors]

**Pos.4 - Static Torque Code** [see Specification Data]

21, 32, 43, 63

**Pos.5 - Output Shaft Extensions\*** [see page 10]

- C** - 1 1/4"[31,75] straight, Parallel key
- G** - 1 1/4"[31,75] 14T Splined
- S** - 1"[25,4] SAE 6B Splined
- T** - 1 1/4"[31,75] SAE J501 Tapered

**Pos.6 - Option [Paint]\*\***

- omit - no Paint
- P** - Painted
- PC** - Corrosion Protected Paint

**Pos.7 - Design Series**

- omit - Factory specified

Notes: \* For Max. Torque values see data on page 10. The permissible output torque for shafts must not be exceeded!

\*\* Color at customer's request.


The Disc Brakes are mangano phosphatized as standard.

**ATTENTION:**

1. Hydraulic brake is delivered without oil ( it is lubricated only).
2. In all brakes, friction discs and separators should be lubricated. Space is filled with 3.05 ÷ 7.32 in<sup>3</sup> [50 ÷ 120 cm<sup>3</sup>] mineral oil HLP (DIN 51524) or HM (ISO 6743/4).

**HYDRAULIC DISC BRAKE TYPE LBS/314  
FOR FLANGE ATTACHMENT TO MLHTS HYDRAULIC MOTORS**

**C Square Mount**



**C** : Brake release Port - 7/16-20UNF, deep .47 [12]

**D** : Drainage tap - 9/16-18UNF, deep .51 [13]

▽ - Place for attachment  
(tightening torque for screws 4x 1/2-13UNC, 1 1/4 in [31,8 mm] long ANSI B 18.3-76: 620 lb-in [7 daNm])

▽▽ - Place for attachment




**SPECIFICATION DATA**

Description LBS/314(315) -... LBV/314(315)-...		21	29	43	65	85	110	130
*Min. Static Torque	lb-in [daNm]	1593-2036 [18-23]	2478-2921 [28-33]	3717-4071 [42-46]	5399-6196 [61-70]	7346-8143 [83-92]	9559-10444 [108-118]	11152-12037 [126-136]
Opening Pressure	min	58-72 [4-5]	87-101 [6-7]	130-145 [9-10]	188-217 [13-15]	261-290 [18-20]	333-362 [23-25]	391-420 [27-29]
	max	4350 [300]						
Min. oil quantity for brake releasing	in. <sup>3</sup> [cm <sup>3</sup> ]	.488 - .549 [8-9]						
Oil quantity	in. <sup>3</sup> [cm <sup>3</sup> ]	9.15 - 18.3 [150-300]						
Max. Pressure in drain space	PSI [bar]	72 [5]						
Weight for .../314 for .../315	lb.[kg]	52.9 [24] 55.1 [25]						

\*Static torque is obtained at working pressure - 0 PSI [0 bar].

**HYDRAULIC DISC BRAKE TYPE LBS/315  
FOR FLANGE ATTACHMENT TO MLHTS HYDRAULIC MOTORS**

**W** Wheel Mount



▽ - Place for attachment  
(tightening torque for screws 4x 1/2-13UNC, 1 1/4 in [31,8 mm] long ANSI B 18.3-76: 620 lb-in [7 daNm])


▽▽ - Place for attachment

**C** : Brake release Port - 7/16-20UNF, deep .472 [12]


**D** : Drainage tap - 9/16-18UNF, deep .512 [13]

**LOAD CURVE**

**Version LB... /314**




**Version LB... /315**





**HYDRAULIC DISC BRAKE TYPE LBV/314  
FOR FLANGE ATTACHMENT TO MLHTV HYDRAULIC MOTORS**

**C Square Mount**




▽ - Place for attachment  
(tightening torque for screws 4xM14 DIN 912:  
1020 lb-in [11,5 daNm])  
▽▽ - Place for attachment

**C** : Brake release Port - 7/16-20UNF, deep .47 [12]  
**D,T** : Drainage tap - 9/16-18UNF, deep .51 [13]

**HYDRAULIC DISC BRAKE TYPE LBV/315  
FOR FLANGE ATTACHMENT TO MLHTV HYDRAULIC MOTORS**

**W Wheel Mount**




▽ - Place for attachment  
(tightening torque for screws 4xM14 DIN 912:  
1020 in-lb [11,5 daNm])  
▽▽ - Place for attachment

**C** : Brake release Port - 7/16-20UNF, deep .47 [12]  
**D,T** : Drainage tap - 9/16-18UNF, deep .51 [13]

**OUTPUT SHAFT EXTENSIONS for LB.../314, 315**


**C**

1½"[38,1] straight, Parallel key 3/8"x3/8"x2¼" BS46  
Max. Torque 11750 lb-in [133 daNm]




**G**

17T Splined, 1½" [38,1] ANS B92.1-1976  
Max. Torque 11750 lb-in [133 daNm]




**M**

ø40 straight, Parallel key A12x8x70 DIN 6885  
Max. Torque 11750 lb-in [133 daNm]



**T**


SAE J501 Tapered 1:8  
Parallel key 7/16"x7/16"x1¼" BS46  
Max. Torque 18650 lb-in [210 daNm]



**INTERNAL SPLINE DATA FOR THE ATTACHED COMPONENT**

Standard ANS B92.1-1970, class 5  
[m=2.1166]

Fillet Root Side Fit		LBS(V)/289 LBS(V)/290		LBS(V)/314 LBS(V)/315	
		inch	mm	inch	mm
Number of Teeth	z	12	12	16	16
Diametral Pitch	DP	12/24	12/24	12/24	12/24
Pressure Angle		30°	30°	30°	30°
Pitch Dia.	D	1	25,4	1.3333	33,8656
Major Dia.	D <sub>ri</sub>	1.1 + 1.098	28,0 <sup>-0,1</sup>	1.5275±1.5118	38,4 <sup>+0,4</sup>
Minor Dia.	D <sub>i</sub>	.9068 ± .9055	23,0 <sup>+0,033</sup>	1.2673±1.2657	32,15 <sup>+0,06</sup>
Space Width [Circular]	Lo	.1704 ± .1688	4,308±0,020	.1763±.1792	4,516±0,037
Fillet Radius	R	.008	0,2	.02	0,5
Max. Measurement between Pins	L	.699 ± .694	17,62 <sup>+0,15</sup>	1.063±1.059	26,9 <sup>+0,10</sup>
Pin Dia.	d	.19039±.19031	4,835±0,001	.19026±.19034	4,835±0,001
Corrected	x,m	+0,031	+0,8	+0,039	+1,0



**ORDER CODE for LBS(LBV)/314 and 315**

	1	2	3	4	5	6	7
<b>L B</b>			/	-			

**Pos.1 - Type**

- S** - Disc Brake for short motor **S**- MLHTS
- V** - Disc Brake for very short motor **V**- MLHTV

**Pos.2 - Output Face**

- C** - Square Mount [only for LBS(LBV)/314]
- W** - Wheel Mount [only for LBS(LBV)/315]

**Pos.3 - Design Code**

- 314** - for MLHTS and MLHTV Motors
- 315** - for MLHTS and MLHTV Motors  
[Wheel Mounting Motors]

**Pos.4 - Static Torque Code [see Specification Data]**

21, 29, 43, 65, 85, 110, 130

**Pos.5 - Output Shaft Extensions\***

- C** - 1½" [38,10] straight, Parallel key
- G** - 1½" [38,10] 17T Splined
- M** - 40 mm straight, Parallel key
- T** - 1¾"[44,50] SAE J501 Tapered

**Pos.6 - Option [Paint]\*\***

- omit - no Paint
- P** - Painted
- PC** - Corrosion Protected Paint

**Pos.7 - Design Series**

- omit - Factory specified

Notes: \* For Max. Torque values see data on **page 15**. The permissible output torque for shafts must not be exceeded!

\*\* Color at customer's request.

The Disc Brakes are mangano phosphatized as standard.


**ATTENTION:**

1. Hydraulic brake is delivered without oil ( it is lubricated only).
2. In all brakes, friction discs and separators should be lubricated. Space is filled with 9.15 ÷ 18.3 in<sup>3</sup> [150 ÷ 300 cm<sup>3</sup>] mineral oil HLP (DIN 51524) or HM (ISO 6743/4).

# HYDRAULIC DISC BRAKES B...R- Wet

B...R brake is designed to be mounted to the wheels of low-speed agricultural and construction vehicles.

The advantage of these brakes is that despite the smallest possible dimensions they preserve long-term life of the bearings at high radial shaft load.



## SPECIFICATION DATA


Type	B35R	B55R
Static Torque of Brake, lb-in [daNm]*	3100 [35]	4870 [55]
Initial Release Pressure, PSI [bar]	232 [16]	232 [16]
Full Release Pressure, PSI [bar]	275 [19]	275 [19]
Max. Operating Pressure, PSI [bar]	3480 [240]	3480 [240]
Max. Speed, RPM	90	90
Cont. Radial Shaft Load lbs [daN]**	1125 [500]	1125 [500]
Max. Radial Shaft Load lbs [daN]***	1575 [700]	2030 [900]

\* At 0 PSI [0 bar] back pressure

\*\* At radial shaft load of 1125 lbs [500 daN], applied at center-line of the key and speed of rotation 90 RPM, the bearing life is 1000 hours.

\*\*\* The permissible values of radial shaft load may occur for max. 10% of every minute

## DIMENSIONS AND MOUNTING DATA



C : Brake Release Port -7/16-20 UNF  
SAE J1926-1/ISO 11926-1


D : Drainage Tap - 7/16-20 UNF



# HYDRAULIC DISC BRAKES B...T- Wet

B..T brake is designed to be mounted to the wheels of low-speed agricultural and construction vehicles.

The advantage of these brakes is that despite the smallest possible dimensions they preserve long-term life of the bearings at high radial shaft load.



## SPECIFICATION DATA


Type	B50T	B55T	B60T	B65T	B85T
Static Torque of Brake, lb-in [daNm]*	4425 [50]	4870 [55]	5310 [60]	5750 [65]	7525 [85]
Initial Release Pressure, PSI [bar]	232 [16]	232 [16]	232 [16]	246 [17]	260 [18]
Full Release Pressure, PSI [bar]	275 [19]	275 [19]	275 [19]	290 [20]	320 [22]
Max. Operating Pressure, PSI [bar]	3480 [240]	3480 [240]	3480 [240]	3480 [240]	3480 [240]
Max. Speed, RPM	60	60	60	60	60
Cont. Radial Shaft Load lbs [daN]**	2250 [1000]	2250 [1000]	2250 [1000]	2250 [1000]	2250 [1000]
Max. Radial Shaft Load lbs [daN]***	4830 [2150]	4830 [2150]	4830 [2150]	4830 [2150]	4830 [2150]

\* At 0 PSI [0 bar] back pressure

\*\* At radial shaft load of 2250 lbs [1000 daN], applied at center-line of the key and speed of rotation 60 RPM, the bearing life is 1000 hours.

\*\*\* The permissible values of radial shaft load may occur for max. 10% of every minute

## DIMENSIONS AND MOUNTING DATA



**C** : Brake Release Port -7/16-20 UNF  
SAE J1926-1/ISO 11926-1

**D** : Drainage Tap - 7/16-20 UNF






# HYDRAULIC MOTOR-BRAKES B/HR




## APPLICATION

- » Conveyors
- » Feeding mechanism of robots and manipulators
- » Metal working machines
- » Textile machines
- » Agricultural machines
- » Food industries
- » Wood working and sawmill machinery etc.



## CONTENTS

Specification data .....	20
Dimensions and mounting. ....	21
Shaft versions .....	21
Permissible shaft loads.....	22
Order code .....	22



## OPTIONS

- » Model - Spool valve, roll-gerotor
- » Fully integrated friction disk brake;
- » Side ports
- » Shafts - straight, splined and tapered
- » Manifold ports.


## GENERAL

<b>Displacement,</b>	in <sup>3</sup> /rev [cm <sup>3</sup> /rev]	24.4 [397]
<b>Max. Speed,</b>	[RPM]	600
<b>Max. Torque,</b>	lb-in [daNm]	cont. 4250 [48] int. 4870 [55]
<b>Max. Output,</b>	HP [kW]	20.1 [15]
<b>Max. Pressure Drop,</b>	PSI [bar]	cont. 2030 [140] int. 2540 [175]
<b>Max. Oil Flow,</b>	GPM [lpm]	20 [75,7]
<b>Min. Speed,</b>	[RPM]	10
<b>Pressure fluid</b>		Mineral based- HLP(DIN 51524) or HM(ISO 6743/4)
<b>Temperature range,</b>	°F [°C]	-40÷284 [-40÷140]
<b>Optimal Viscosity range, SUS [mm<sup>2</sup>/s]</b>		98÷347 [20÷75]
<b>Filtration</b>		ISO code 20/16 (Min. recommended fluid filtration of 25 microns)

### Oil flow in drain line

Pressure drop PSI [bar]	Viscosity SUS [mm <sup>2</sup> /s]	Oil flow in drain line GPM [lpm]
1450 [100]	98 [20]	.660 [2,5]
	164 [35]	.476 [1,8]
2030 [140]	98 [20]	.925 [3,5]
	164 [35]	.740 [2,8]

### Pressure Losses



**SPECIFICATION DATA**

Type		B/HR 80	B/HR 100	B/HR 125	B/HR 160	B/HR 200	B/HR 250	B/HR 315	B/HR 400
<b>Displacement, in<sup>3</sup>/rev [cm<sup>3</sup>/rev]</b>		4.90 [80,3]	6.09 [99,8]	7.67 [125,7]	9.74 [159,6]	12.19 [199,8]	15.26 [250,1]	19.26 [315,7]	24.23 [397]
<b>Max. Speed, [RPM]</b>	Cont.	500	500	475	375	300	240	190	150
	Int.*	600	600	600	470	375	300	240	191
<b>Max. Torque in-lb [daNm]</b>	Cont.	1390 [15,7]	1750 [19,8]	2210 [25,0]	2830 [32,0]	3045 [34,4]	3540 [40,0]	3850 [43,5]	4250 [48,0]
	Int.*	1725 [19,5]	2125 [24,0]	2655 [30,0]	3450 [39,0]	3450 [39,0]	4160 [47,0]	4515 [51,0]	4870 [55,0]
<b>Max. Output HP [kW]</b>	Cont.	14 [10,5]	14 [10,5]	14 [10,5]	13.7 [10,2]	12.6 [9,4]	10.7 [8]	8.7 [6,5]	8.2 [6,1]
	Int.*	20.1 [15]	20.1 [15]	20.1 [15]	18.8 [14]	18.7 [14]	15.4 [11,5]	12.1 [9]	11 [8,2]
<b>Max. Pressure Drop PSI [bar]</b>	Cont.	2030 [140]	2030 [140]	2030 [140]	2030 [140]	1810 [125]	1595 [110]	1450 [100]	1305 [90]
	Int.*	2540 [175]	2540 [175]	2540 [175]	2540 [175]	2250 [155]	2030 [140]	1810 [125]	1520 [105]
<b>Max. Oil Flow GPM [lpm]</b>	Cont.	10.6 [40]	13 [50]	16 [60,6]	16 [60,6]	16 [60,6]	16 [60,6]	16 [60,6]	16 [60,6]
	Int.*	13 [50]	16 [60,6]	20 [75,7]	20 [75,7]	20 [75,7]	20 [75,7]	20 [75,7]	20 [75,7]
<b>Max. Inlet Pressure PSI [bar]</b>	Cont.	2030 [140]	2030 [140]	2030 [140]	2030 [140]	2030 [140]	2030 [140]	2030 [140]	2030 [140]
	Int.*	2540 [175]	2540 [175]	2540 [175]	2540 [175]	2540 [175]	2540 [175]	2540 [175]	2540 [175]
<b>Max. Return Pressure, PSI [bar]</b>	Cont.	2030 [140]	2030 [140]	2030 [140]	2030 [140]	2030 [140]	2030 [140]	2030 [140]	2030 [140]
	Int.*	2540 [175]	2540 [175]	2540 [175]	2540 [175]	2540 [175]	2540 [175]	2540 [175]	2540 [175]
<b>Max. Starting Pressure with Unloaded Shaft, PSI [bar]</b>		145 [10]	145 [10]	130 [9]	102 [7]	73 [5]	58 [4]	44 [3]	44 [3]
<b>Min. Starting Torque in-lb [daNm]</b>	At max.press. drop Cont.	1060 [12]	1420 [16]	1770 [20]	2270 [25,6]	2620 [29,5]	2510 [28,3]	2840 [32]	3170 [35,8]
	At max.press. drop Int.*	1310 [14,8]	1780 [20,1]	1930 [21,8]	2860 [32,3]	3150 [35,6]	3400 [38,4]	4580 [51,7]	4040 [45,6]
<b>Min. Speed***, [RPM]</b>		10	10	10	10	10	10	10	10
<b>Static Torque of Brake, in-lb [daNm]</b>		4890 [55]							
<b>Min. Brake Release Pressure****, PSI [bar]</b>		160 [13]							
<b>Max. Opening Pressure, PSI [bar]</b>		2900 [200]							

\* Intermittent operation: the permissible values may occur for max. 10% of every minute.

\*\* Peak load: the permissible values may occur for max. 1% of every minute.


\*\*\* For speeds lower than given, consult factory or your regional manager.

\*\*\*\* Motor-brakes must always have a drain line. The brake release pressure is the difference between the pressure in the brake release line and the pressure in the drain line.


- Intermittent speed and intermittent pressure drop must not occur simultaneously.
- Recommended filtration is per ISO cleanliness code 20/16. A nominal filtration of 25 micron or better.
- Recommend using a premium quality, anti-wear type mineral based hydraulic oil HLP(DIN51524) or HM (ISO 6743/4). If using synthetic fluids consult the factory for alternative seal materials.
- Recommended minimum oil viscosity 70 SUS [13 mm<sup>2</sup>/s] at 122°F [50°C].
- Recommended maximum system operating temperature is 180°F [82°C].
- To assure optimum motor life fill with fluid prior to loading and run at moderate load and speed for 10-15 minutes.

**DIMENSIONS AND MOUNTING DATA**

Version **1**



Version **4**



Type	Lmax, in [mm]	L <sub>1</sub> , in [mm]
B/HR 80	8.47 [215,0]	.55 [14,0]
B/HR 100	8.58 [218,0]	.69 [17,4]
B/HR 125	8.76 [222,5]	.86 [21,8]
B/HR 160	9.00 [228,5]	1.09 [27,8]
B/HR 200	9.27 [235,5]	1.37 [34,8]
B/HR 250	9.61 [244,0]	1.71 [43,5]
B/HR 315	10.06 [255,5]	2.16 [54,8]
B/HR 400	10.63 [270,0]	2.73 [69,4]

**Standard Rotation**

Viewed from Shaft End

Port A Pressurized - **CW**

Port B Pressurized - **CCW**

**Reverse Rotation**

Viewed from Shaft End

Port A Pressurized - **CCW**


Port B Pressurized - **CW**

	Versions	
	<b>1</b>	<b>4</b>
<b>C</b>	4x 5/16-18UNC	-
<b>P<sub>(A,B)</sub></b>	2x.39 Dia [2x10]	2x 7/8-14UNF
<b>T</b>	7/16 -20UNF	7/16 -20UNF

**SHAFT EXTENSIONS**


**C**

1" [25,4] straight, Woodruff key 1/4"x1" SAE J502  
Max. Torque 3900 in-lb [44 daNm]



**G**

1" [25,4], SAE 6B Splined  
Max. Torque 3900 in-lb [44 daNm]



**PERMISSIBLE SHAFT LOADS**

The permissible radial shaft load  $P_{rad}$  depends on the speed RPM and distance  $L$  from the point of load to the mounting flange.

$$\text{Radial Shaft Load } P_{rad} = \frac{650}{\text{RPM}} \times \frac{24800}{97+L}, \text{ daN}^*$$



\*  $L$  - in mm.

$$\text{Radial Shaft Load: } P_{rad} = \frac{1460}{\text{RPM}} \times \frac{976}{3.82+L}, \text{ lbs}^*$$

\*  $L$  - in inch

1. RPM < 200: max Prad=1460 lbs [650 daN]

2. RPM ≥ 200:  $L < 2.2$  in. [55 mm]



**Warning: Drain line should always be used.**

**ORDER CODE**

	1	2	3	4	5
<b>B / H R</b>					

**Pos.1 - Displacement code\***

<b>80</b>	- 4.90 [ 80,3] in <sup>3</sup> /rev [cm <sup>3</sup> /rev]
<b>100</b>	- 6.09 [ 99,8] in <sup>3</sup> /rev [cm <sup>3</sup> /rev]
<b>125</b>	- 7.67 [125,7] in <sup>3</sup> /rev [cm <sup>3</sup> /rev]
<b>160</b>	- 9.74 [159,6] in <sup>3</sup> /rev [cm <sup>3</sup> /rev]
<b>200</b>	- 12.19 [199,8] in <sup>3</sup> /rev [cm <sup>3</sup> /rev]
<b>250</b>	- 15.26 [250,1] in <sup>3</sup> /rev [cm <sup>3</sup> /rev]
<b>315</b>	- 19.26 [315,7] in <sup>3</sup> /rev [cm <sup>3</sup> /rev]
<b>400</b>	- 24.23 [397,0] in <sup>3</sup> /rev [cm <sup>3</sup> /rev]

**Pos.2 - Shaft Extensions\*\***

<b>C</b>	- 1" [25,4] straight, Woodruff key
<b>G</b>	- 1" [25,4] SAE 6B Splined

**Pos.3 - Port Size/Type [standard manifold to each]**

<b>1</b>	- side ports, Manifold [5/16-18 UNC Mounting Threads], 7/16-20 UNF
<b>4</b>	- side ports, 2x7/8-14 UNF, O-ring, 7/16-20 UNF

**Pos. 4 - Special Features [See page 55]**

**Pos. 5 - Design Series**

omit - Factory specified

Notes : \* For the Performance Data please look at "M+S Hydraulic" Catalogue for MLHR motors.


\*\* The permissible output torque for shafts must not be exceeded!

The hydraulic motors are mangano-phosphatized as standard.

# HYDRAULIC MOTOR-BRAKES RWB

## APPLICATION

- » Conveyors
- » Feeding mechanism of robots and manipulators
- » Metal working machines
- » Textile machines
- » Agricultural machines
- » Food industries
- » Grass cutting machinery etc.



## CONTENTS

Specification data ..... 24  
 Dimensions and mounting ..... 25  
 Permissible shaft Seal Pressure ... 26  
 Permissible shaft loads ..... 26  
 Brake Holding Torque..... 27  
 Order code ..... 27

## OPTIONS

- » Model - Spool valve, roll-gerotor
- » Drum brake
- » Shaft seal for high and low pressure
- » SAE, Metric and BSPP ports
- » Other special features


## GENERAL

<b>Max. Displacement,</b> in <sup>3</sup> /rev [cm <sup>3</sup> /rev]	24.4 [397]
<b>Max. Speed,</b> [RPM]	1029
<b>Max. Torque,</b> lb-in [daNm]	cont.: 5400 [61] int.: 6100 [69]
<b>Max. Output,</b> HP [kW]	20.1 [15]
<b>Max. Pressure Drop,</b> PSI [bar]	cont.: 2540 [175] int.: 2900 [200]
<b>Max. Oil Flow,</b> GPM [lpm]	23.8 [90]
<b>Min. Speed,</b> [RPM]	10
<b>Pressure fluid</b>	Mineral based- HLP(DIN 51524) or HM(ISO 6743/4)
<b>Temperature range,</b> °F [°C]	-40÷284 [-40÷140]
<b>Optimal Viscosity range, SUS [mm<sup>2</sup>/s]</b>	98÷347 [20÷75]
<b>Filtration</b>	ISO code 20/16 (Min. recommended fluid filtration of 25 microns)

### Oil flow in drain line

Pressure drop PSI [bar]	Viscosity SUS [mm <sup>2</sup> /s]	Oil flow in drain line GPM [lpm]
1450 [100]	98 [20]	.660 [2,5]
	164 [35]	.476 [1,8]
2030 [140]	98 [20]	.925 [3,5]
	164 [35]	.740 [2,8]

### Pressure Losses





## SPECIFICATION DATA

Type	RWB 50	RWB 80	RWB 100	RWB 125	RWB 160	RWB 200	RWB 250	RWB 315	RWB 400	
<b>Displacement, in<sup>3</sup>/rev</b> [cm <sup>3</sup> /rev]	3.14 [51,5]	4.90 [80,3]	6.09 [99,8]	7.67 [125,7]	9.74 [159,6]	12.19 [199,8]	15.26 [250,1]	19.26 [315,7]	24.4 [397]	
<b>Max. Speed,</b> [RPM]	Cont.	775	750	600	475	375	300	300	240	190
	Int.*	1029	940	750	600	470	375	360	285	2261
<b>Max. Torque</b> [lb-in [daNm]	Cont.	900 [10]	1770 [20]	2125 [24]	2655 [30]	3450 [39]	4000 [45]	4780 [54]	4870 [55]	5400 [61]
	Int.*	1150 [13]	1947 [22]	2480 [28]	3010 [34]	3805 [43]	4425 [50]	5400 [61]	5580 [63]	6100 [69]
	Peak**	1505 [17]	2390 [27]	2832 [32]	3275 [37]	4070 [46]	4960 [56]	6280 [71]	7350 [83]	7700 [87]
<b>Max. Output</b> [HP [kW]	Cont.	9.5 [7]	17 [12,5]	17.4 [13]	16.8 [12,5]	15.4 [11,5]	14.8 [11]	13.4 [10]	12 [9]	10.5 [7,8]
	Int.*	11.9 [8,5]	20.1 [15]	20.1 [15]	19.5 [14,5]	18.8 [14]	17.4 [13]	16.1 [12]	14.8 [11]	14.2 [10,6]
<b>Max. Pressure Drop</b> [PSI [bar]	Cont.	2030 [140]	2540 [175]	2540 [175]	2540 [175]	2540 [175]	2540 [175]	2540 [175]	1960 [135]	1600 [110]
	Int.*	2540 [175]	2900 [200]	2900 [200]	2900 [200]	2900 [200]	2900 [200]	2900 [200]	2320 [160]	2030 [140]
	Peak**	3260 [225]	3260 [225]	3260 [225]	3260 [225]	3260 [225]	3260 [225]	3260 [225]	3045 [210]	2540 [175]
<b>Max. Oil Flow</b> [GPM [lpm]	Cont.	11 [40]	15.9 [60]	15.9 [60]	15.9 [60]	15.9 [60]	15.9 [60]	19.8 [75]	19.8 [75]	19.8 [75]
	Int.*	13 [50]	19.8 [75]	19.8 [75]	19.8 [75]	19.8 [75]	19.8 [75]	23.8 [90]	23.8 [90]	23.8 [90]
<b>Max. Inlet Pressure</b> [PSI [bar]	Cont.	2540 [175]	2540 [175]	2540 [175]	2540 [175]	2540 [175]	2540 [175]	2540 [175]	2540 [175]	2540 [175]
	Int.*	2900 [200]	2900 [200]	2900 [200]	2900 [200]	2900 [200]	2900 [200]	2900 [200]	2900 [200]	2900 [200]
	Peak**	3260 [225]	3260 [225]	3260 [225]	3260 [225]	3260 [225]	3260 [225]	3260 [225]	3260 [225]	3260 [225]
<b>Max. Return Pres- sure with Drain Line</b> [PSI [bar]	Cont.	2540 [175]	2540 [175]	2540 [175]	2540 [175]	2540 [175]	2540 [175]	2540 [175]	2540 [175]	2540 [175]
	Int.*	2900 [200]	2900 [200]	2900 [200]	2900 [200]	2900 [200]	2900 [200]	2900 [200]	2900 [200]	2900 [200]
	Peak**	3260 [225]	3260 [225]	3260 [225]	3260 [225]	3260 [225]	3260 [225]	3260 [225]	3260 [225]	3260 [225]
<b>Max. Starting Pressure with Unloaded Shaft, PSI [bar]</b>	145 [10]	145 [10]	145 [10]	130 [9]	102 [7]	73 [5]	73 [5]	73 [5]	73 [5]	
<b>Min. Starting Torque</b> [lb-in [daNm]	At max.press.									
	drop Cont.	710 [8]	1330 [15]	1770 [20]	2215 [25]	2832 [32]	3630 [41]	4425 [50]	4425 [50]	4425 [50]
	At max.press. drop Int.*	885 [10]	1505 [17]	2035 [23]	2480 [28]	3275 [37]	4070 [46]	4870 [55]	5840 [66]	5400 [61]
<b>Min. Speed***, [RPM]</b>	10	10	10	9	7	5	6	5	5	

\* Intermittent operation: the permissible values may occur for max. 10% of every minute.


\*\* Peak load: the permissible values may occur for max. 1% of every minute.

\*\*\* For speeds lower than given, consult factory or your regional manager.


- Intermittent speed and intermittent pressure drop must not occur simultaneously.
- Recommended filtration is per ISO cleanliness code 20/16. A nominal filtration of 25 micron or better.
- Recommend using a premium quality, anti-wear type mineral based hydraulic oil HLP(DIN51524) or HM (ISO 6743/4).  
If using synthetic fluids consult the factory for alternative seal materials.
- Recommended minimum oil viscosity 70 SUS [13 mm<sup>2</sup>/s] at 122°F [50°C].
- Recommended maximum system operating temperature is 180°F [82°C].
- To assure optimum motor life fill with fluid prior to loading and run at moderate load and speed for 10-15 minutes.

**DIMENSIONS AND MOUNTING DATA**

**B 5 Bolt Brake Drum**




**A 4 Bolt Brake Drum**




**RW.../B2V-2R**

**V-2**  
Lever Type





**RW.../A2V-1L**


**V-1**  
Lever Type



**Wheel Bolts Type**



in [mm]



Type	Lmax, in [mm]	L1, in [mm]
RWB 50	4.25 [108,0]	.35 [9,0]
RWB 80	4.45 [113,0]	.55 [14,0]
RWB 100	4.59 [116,5]	.69 [17,4]
RWB 125	4.74 [120,5]	.86 [21,8]
RWB 160	4.98 [126,5]	1.09 [27,8]
RWB 200	5.26 [133,5]	1.37 [34,8]
RWB 250	5.61 [142,5]	1.71 [43,5]
RWB 315	6.04 [153,5]	2.16 [54,8]
RWB 400	6.63 [168,5]	2.73 [69,4]


**Standard Rotation**  
Viewed from Shaft End  
Port A Pressurized - **CW**  
Port B Pressurized - **CCW**

**Reverse Rotation**  
Viewed from Shaft End  
Port A Pressurized - **CCW**  
Port B Pressurized - **CW**

	Versions		
	2	3	4
P(A,B)	2xG½	2xM22x1,5	2x7/8-14UNF O-ring
T	G¼	M14x1,5	7/16-20UNF O-ring

**PERMISSIBLE SHAFT LOADS RWB**

The curve applies to a B10 bearing life of 2000 hours when mineral-based hydraulic oil with sufficient content of anti-wear additives is used.




1. Permissible radial shaft load
2. Drawing by n= 50 RPM
3. Drawing by n=100 RPM
4. Drawing by n=200 RPM
5. Drawing by n=400 RPM

**MAX. PERMISSIBLE SHAFT SEAL PRESSURE**


**RWB...; RWB...UK motors with drain connection:**

The shaft seal pressure equals the pressure in the drain line.




**RWB...1 motors without drain connection:**

The shaft seal pressure never exceeds the pressure in the return line.




**RWB...U motors with high pressure seal and drain connection:**

The shaft seal pressure equals the pressure in the drain line.




**Max. return pressure without drain line or max. pressure in the drain line**



- 1: Drawing for Standard Shaft Seal
  - 2: Drawing for High Pressure Seal ("U" Seal)
- - continuous operations  
- - - - - intermittent operations


**BRAKE HOLDING TORQUE**



$P_L$  - Brake Lever Load  
 $M_C$  - Brake Torque  
 $M_L$  - Brake Lever Torque  
 $M_C$  max=68 daNm

**SHAFT**

1 1/4" [31,75], SAE J501 Tapered  
 Parallel key 5/16"x 5/16"x1"  
 Max. Torque 6815 lb-in [77 daNm]



Requirement max. Torque must not be exceeded.

**ORDER CODE**

1	2	3	4	5	6	7	8	9	10	10	12
RWB					/						

**Pos.1 - Displacement code**

50	- 3.14 in <sup>3</sup> /rev [51,5 cm <sup>3</sup> /rev]
80	- 4.90 in <sup>3</sup> /rev [80,3 cm <sup>3</sup> /rev]
100	- 6.09 in <sup>3</sup> /rev [99,8 cm <sup>3</sup> /rev]
125	- 7.67 in <sup>3</sup> /rev [125,7 cm <sup>3</sup> /rev]
160	- 9.74 in <sup>3</sup> /rev [159,6 cm <sup>3</sup> /rev]
200	- 12.19 in <sup>3</sup> /rev [199,8 cm <sup>3</sup> /rev]
250	- 15.26 in <sup>3</sup> /rev [250,1 cm <sup>3</sup> /rev]
315	- 19.26 in <sup>3</sup> /rev [315,7 cm <sup>3</sup> /rev]
400	- 24.40 in <sup>3</sup> /rev [397,0 cm <sup>3</sup> /rev]

**Pos.2 - Shaft Seal Version**

omit	- Standard shaft seal
U	- High pressure shaft seal without check valves
UK	- High pressure shaft seal with check valves

**Pos.3 - Drain Port**

omit	- with drain port
1	- without drain port

**Pos.4 - Port Size/Type [standard manifold to each]**

2	- side ports, 2xG 1/2, G1/4, BSP thread, ISO 228
3	- side ports, 2xM22x1,5, M14x1,5, metric thread
4	- side ports, 2x7/8-14 UNF, O-ring, 7/16-20 UNF

**Pos.5 - Special Features**

omit	- none
LL	- Low Leakage
LSV	- Low Speed Valve

**Pos. 6 - Rotation**

omit	- Standard Rotation
R	- Reverse Rotation

**Pos. 7 - Drum type**

A	- Drum brake with bolts 4x1/2-20 UNF on 4 Dia. [ø101,6]
B	- Drum brake with bolts 5x1/2-20 UNF on 4.5 Dia. [ø114,3]

**Pos. 8 - Drum Bolt type**

1	- 1/2-20 UNF-2A L= .787 in [20 mm]
2	- 1/2-20 UNF-2A L=1.259 in [32 mm]
3	- 1/2-20 UNF-2A L=2.362 in [60 mm]

**Pos. 9 - Lever Type**

V-1	- Vertical Brake Lever 2x.33 Dia. [ø8,4] - 2 in [50,8 mm]
V-2	- Vertical Brake Lever .338 Dia. [ø8,6] - 2.76 in [70 mm]

**Pos.10 - Lever Position**

R	- Right
L	- Left

**Pos.11 - Option (Paint)\***


omit	- no Paint
P	- Painted
PC	- Corrosion Protected Paint

**Pos.12 - Design Series**

omit	- Factory specified
------	---------------------


The hydraulic motor-brakes are manganese-phosphatized as standard.

# HYDRAULIC MOTOR-BRAKES SW500B350V




## APPLICATION

- » Wheel drives
- » Conveyors
- » Rotators
- » Positioners
- » Winches
- » Swing drives
- » Door openers



## CONTENTS

Specification data .....	28
Dimensions and mounting .....	29
Permissible shaft loads .....	29
Function diagrams .....	30



## SPECIFICATION DATA


Type	SW500B350V
<b>Displacement, in<sup>3</sup>/rev [cm<sup>3</sup>/rev]</b>	29 [475,3]
<b>Max. Speed, RPM</b>	16
Cont.	
Int.*	25
<b>Max. Torque, lb-in [daNm]</b>	7260 [82]
Cont.	
Int.*	8420 [95]
<b>Max. Output, HP [kW]</b>	1.3 [0,9]
Cont.	
Int.*	3.3 [2,4]
<b>Max. Pressure Drop, PSI [bar]</b>	1800 [125]
Cont.	
Int.*	2100 [145]
<b>Max. Oil Flow, GPM [lpm]</b>	2 [8]
Cont.	
Int.*	3 [12]
<b>Max. Return Pressure without Drain Line or Max. Pressure in Drain Line, PSI [bar]</b>	1450 [100]
<b>Min. Starting Torque, lb-in [daNm]</b>	6400 [72]
At max. press. drop Cont.	
At max. press. drop Int.*	6650 [75]
<b>Min. Speed**, RPM</b>	5
<b>Static Torque for the Brake***, lb-in [daNm]</b>	14 515 [164]
<b>Release Pressure ±10%, PSI [bar]</b>	363...406 [25...28]
initial	
full	449.6 [31]
<b>Max. Steering Pressure, PSI [bar]</b>	3553 [245]
<b>Max. Pressure in Drain Space for the Brake, PSI [bar]</b>	7 [0,5]
<b>Pilot Ratio for the Valve</b>	4,25:1

\* Intermittent operation: the permissible values may occur for max. 10% of every minute.


\*\* For speeds of 5 RPM lower than given, consult factory or your regional manager.

\*\*\* Static torque is obtained at working pressure - 0 PSI [0 bar].

**DIMENSIONS AND MOUNTING**




**A,B:** 7/16-20 UNF  
**D :** 1/4-18 NPTF



**Note:** For different port's thread please contact with "M+S Hydraulic".

**PERMISSIBLE SHAFT LOADS**


The curve applies to a B10 bearing life of 3000 hours at 40 RPM.





**FUNCTION DIAGRAMS**

**SW 500**



The working area  
for SW500B350V

**ORDER CODE**

1	2	3	4	5	6	7	8
S	W	500	B	350	V		


- Pos.1 - **Type**  
S - Motor MLHS
- Pos.2 - **Displacement code**
- Pos.3 - **Brake**
- Pos.4 - **Brake Type**

- Pos.5 - **Shaft Extension**  
omit - 17T PITCH splined
- Pos.6 - **Valve**
- Pos.7 - **Special Features** (see page 55)
- Pos.8 - **Design Series**  
omit - Factory specified


The motor-brakes are mangano-phosphatized as standard.

# HYDRAULIC MOTOR-BRAKES TW500B350...V

## APPLICATION




- » Wheel drives
- » Conveyors
- » Rotators
- » Positioners
- » Winches
- » Swing drives
- » Door openers




## CONTENTS

Specification data .....	31
Dimensions and mounting .....	32
Function diagrams .....	33
Order code .....	33

Motor-Brake  
Type TW500B350V



Motor-Brake  
Type TW500B350CV



## SPECIFICATION DATA



Type		TW500B350...
Displacement, in <sup>3</sup> /rev [cm <sup>3</sup> /rev]		29 [475]
Max. Speed, RPM	Cont.	40
	Int.*	60
Max. Torque, lb-in [daNm]	Cont.	10 000 [114]
	Int.*	12 000 [135]
Max. Output, HP [kW]	Cont.	5.4 [4,1]
	Int.*	9.39 [7,0]
Max. Pressure Drop, PSI [bar]	Cont.	2500 [170]
	Int.*	2900 [200]
Max. Oil Flow, GPM [lpm]	Cont.	5.3 [20]
	Int.*	9.2 [35]
Max. Return Pressure without Drain Line or Max. Pressure in Drain Line, PSI [bar]		1088 [75]
Min. Starting Torque, in-lb [daNm]	At max. press. drop Cont.	8400 [95]
	At max. press. drop Int.*	9940 [112]
Min. Speed**, RPM		5
Static Torque for the Brake***, lb-in [daNm]		14 515 [164]
Release Pressure ±10%, PSI [bar]	initial	326...400 [22,5...27,5]
	full	406...493 [28...34]
Max. Steering Pressure, PSI [bar]		3553 [245]
Max. Pressure in Drain Space for the Brake, PSI [bar]		7 [0,5]
Pilot Ratio for the Valve		4,25:1

\* Intermittent operation: the permissible values may occur for max. 10% of every minute.

\*\* For speeds of 5 RPM lower than given, consult factory or your regional manager.



\*\*\* Static torque is obtained at working pressure - 0 bar [0 PSI].

**DIMENSIONS AND MOUNTING**




Output Shaft for TW500B350V

Valve Block for TW500B350V



Valve Block for TW500B350CV




- A, B** : 2x7/8-14 UNF, .65 [17,5] deep
- D** : 7/16-20 UNF
- C** : G1/4
- A2, X** : 7/16-18 UNF, .475 [12] deep

**Note:** For different port's thread please contact with "M+S Hydraulic".




**PERMISSIBLE SHAFT LOADS**

The curve applies to a B10 bearing life of 3000 hours at 40 RPM.



**FUNCTION DIAGRAMS**

**TW 500**



The working area  
for TW500B350V

**ORDER CODE**

1	2	3	4	5	6	7	8
T	W	500	B	350	V		

- Pos.1 - **Type**  
**S** - Motor MLHT
- Pos.2 - **Displacement code**
- Pos.3 - **Brake**
- Pos.4 - **Brake Type**

- Pos.5 - **Shaft Extension\***  
omit - 17T 5/7 pitch 20° involute  
**C** - Straight key 1/2"x1/2"x1 1/2"
- Pos.6 - **Valve**
- Pos.7 - **Special Features** (see page 55)
- Pos.8 - **Design Series**  
omit - Factory specified

The motor-brakes are manganophosphatized as standard.


# VALVES FOR HYDRAULIC MOTORS

## CONTENTS


Valves for MLHP, MLHR and MLHH type KPBR ... 35  
 Valves for MLHS type KPBS ..... 36  
 Valves for MLHT type KPBT ..... 37  
 Valves for MLHV type KPBV ..... 38  
 Valves for MLHRW and HW type KPBW ..... 39  
 Valves for HP and HR type KPBHR...E ..... 40  
 Valves for HP and HR type KPBHR...D ..... 41  
 Switch valves type KPWR and KPWS ..... 42  
 Switch valves type KPWT and KPWW ..... 43

Crossover Relief Valves ..... 44  
 Valves for MLHP, MLHR and MLHH type KP...R ... 45  
 Valves for MLHS type KP...S ..... 45  
 Valves for MLHT type KP...T ..... 46  
 Valves for MLHV type KP...V ..... 48  
 Valves for MLHRW and HW type KP...W ... 51  
 Cross Port Relief Valves ..... 52  
 Order Code ..... 53


## OVERCENTER VALVES WITH BRAKE CONTROL



Single Overcenter Valves with Brake Control type KPBR ... AE



Single Overcenter Valves with Brake Control type KPBR ... BE



Dual Overcenter Valves with Brake Control type KPBR ... D


## SPECIFICATION DATA

Parameters	Type											
	KPBR...E	KPBS...E	KPBR...D	KPBS...D	KPBW...E	KPBW...D	KPBHR...E	KPBHR...D	KPBT...E	KPBT...D	KPBV...E	KPBV...D
Flow Rate, GPM [lpm]	15.85 [60]						26.4 [100]		52.8 [200]			
Rated PSI Pressure*, [bar]	870÷4060 [60÷280]						1015÷3625 [70÷250]					
Pilot Ratio	4,25:1											
Weight, lb [kg]	6.658 [3,020]	6.39 [2,900]	6.746 [3,060]	6.437 [2,920]	7.724 [3,050]	6.923 [3,140]	5.071 [2,300]	5.291 [2,400]	11.905 [5,400]	12.787 [5,800]	20.283 [9,200]	21.495 [9,750]


\*Pressure Settings are at flow rate of 1.3 GPM [5 lpm] and viscosity 150 SUS [32 mm<sup>2</sup>/s] at 122° F [50 °C].

## PRESSURE LOSSES


### KPBR..., KPBS..., KPBW... and KPBHR...



### KPBT...




### KPBV...




**VALVES FOR MLHP, MLHR, MLHH HYDRAULIC MOTORS**

**SINGLE VALVE KPBR-250/1/E...**



**DUAL VALVE KPBR-250/1/D...**



	Thread Ports - P <sub>(A,B)</sub>	Thread Port - C
-	G1/2 .63 [16] depth	G1/4 .47 [12] depth
M	M22x1,5 .63 [16] depth	M14x1,5 .47 [12] depth
A	7/8 - 14 UNF O-ring .63 [16] depth	7/16 - 20 UNF O-ring .50 [12,7] depth




**Note :** KPBR Blocks are installed directly on MLHP, MLHR and MLHH Motors with four screws 5/16-18UNC, 1.75 long ANSI B 18.3 or M8x45 - 8.8 DIN 912. Tightening torque 168±150 lb-in [1,7<sup>+0,2</sup> daNm].




**VALVES FOR MLHS HYDRAULIC MOTORS**

**SINGLE VALVE KPBS-250/1/E...**




**DUAL VALVE KPBS-250/1/D...**



	Thread Ports - P <sub>(A,B)</sub>	Thread Port - C
-	G1/2 .63 [16] depth	G1/4 .47 [12] depth
M	M22x1,5 .63 [16] depth	M14x1,5 .47 [12] depth
A	7/8 - 14 UNF O-ring .63 [16] depth	7/16 - 20 UNF O-ring .50 [12,7] depth




**Note :** KPBS Blocks are installed directly on MLHS Motors with two screws 3/8-16UNC, 1.75 long ANSI B 18.3 or M10x45 - 8.8 DIN 912. Tightening torque 336÷310 in-lb [3,5<sup>+0,3</sup> daNm].





## VALVES FOR MLHT HYDRAULIC MOTORS

### SINGLE VALVE KPBT-250/1/E...



### DUAL VALVE KPBT-250/1/D...




	Thread Ports - P <sub>(A,B)</sub>	Thread Port - C
-	G3/4 .67 [17] depth	G1/4 .55 [14] depth
M	M27x2 .67 [17] depth	M14x1,5 .55 [14] depth
A	1 1/16-12 UN O-ring .67 [17] depth	7/16 - 20 UNF O-ring .50 [12,7] depth



**Note :** KPBT Blocks are installed directly on MLHT Motors with four screws M10x50 - 8.8 DIN 912. Tightening torque 336±310 lb-in [3,5<sup>+0,3</sup> daNm].



**VALVES FOR MLHV HYDRAULIC MOTORS**

**DUAL VALVE KPBV-250/1/D...**



**SINGLE VALVE KPBV-250/1/AE...**

**SINGLE VALVE KPBV-250/1/BE...**





	Thread Ports - P <sub>(A,B)</sub>	Thread Port - C
-	G 1 .79 [20] depth	G1/4 .55 [14] depth
M	M33x2 .79 [20] depth	M14x1,5 .55 [14] depth
A	1 5/16 - 12 UN O-ring .79 [20] depth	7/16 - 20 UNF O-ring .5 [12,7] depth




**Note :** KPBV Blocks are installed directly on MLHV Motors with four screws M12x70 - 8.8 DIN 912. Tightening torque 620+575 lb-in [6,5<sup>+0,5</sup> daNm].

**VALVES FOR MLHRW and HW HYDRAULIC MOTORS**


**DUAL VALVE KPBW-250/1/D...**




**KPBW-...A**



**SINGLE VALVE KPBW-250/1/AE...**



**SINGLE VALVE KPBW-250/1/BE...**



	Thread Ports - P <sub>(A,B)</sub>	Thread Port - C	Thread Ports - D
-	G1/2 .63 [16] depth	G1/4 .47 [12] depth	G1/2 .47 [12] length
M	M22x1,5 .63 [16] depth	M14x1,5 .47 [12] depth	M22x1,5 .47 [12] length
A	7/8 - 14 UNF O-ring .63 [16] depth	7/16 - 20 UNF O-ring .50 [12,7] depth	7/8 - 14 UNF O-ring .51 [13] length









**Note :** KPBW Blocks assembly to MLHRW or HW motors is done with two screws (thread D) included in the valve set. Tightening torque 710 lb-in [8 daNm].

**VALVES FOR HP, HR HYDRAULIC MOTORS**

**SINGLE VALVE KPBHR-250/1/BE...**

**SINGLE VALVE KPBHR-250/1/AE...**






	Thread Ports - P <sub>(A,B)</sub>	Thread Ports - C
<b>A</b>	7/8 - 14 UNF O-ring .67 [17] deep	7/16 - 20 UNF O-ring .50 [12,7] deep
<b>-</b>	G1/2 .67 [17] deep	G1/4 .55 [14] deep
<b>M</b>	M22x1,5 .67 [17] deep	M14x1,5 .55 [14] deep

**Note :** KPBHR Blocks are installed directly on HP and HR Motors with four bolts 5/16-18UNC, 2.36 long or M8x60 - 8.8 DIN 912. Tightening torque 265±221 lb-in [2,5<sup>+0,5</sup> daNm].

**VALVES FOR HP, HR HYDRAULIC MOTORS**

**DUAL VALVE KPBHR-250/1/D...**




	Thread Ports - P <sub>(A,B)</sub>	Thread Ports - C
<b>A</b>	7/8 - 14 UNF O-ring .67 [17] deep	7/16 - 20 UNF O-ring .50 [12,7] deep
<b>-</b>	G1/2 .67 [17] deep	G1/4 .55 [14] deep
<b>M</b>	M22x1,5 .67 [17] deep	M14x1,5 .55 [14] deep

**Note :** KPBHR Blocks are installed directly on HP and HR Motors with four bolts 5/16-18UNC, 2.36 long or M8x60 - 8.8 DIN 912. Tightening torque 265±221 lb-in [2,5<sup>+0,5</sup> daNm].




**SWITCH VALVES**

**SPECIFICATION DATA**







Parameters	Type	
	KPWR	KPWS
Flow Rate , GPM [lpm]	15.85	[60]
Rated Pressure , PSI [bar]	3625	[250]
Weight , lb	1.874	1.477
	[kg]	[0,850]
		[0,670]



**VALVE FOR MLHP, MLHR, MLHH HYDRAULIC MOTORS  
KPWR**

**VALVE FOR MLHS HYDRAULIC MOTORS  
KPWS**



	Thread Ports - P <sub>(A,B)</sub>	Thread Port - C
-	G1/2 .67 [17] depth	G1/4 .55 [14] depth
M	M22x1,5 .67 [17] depth	M14x1,5 .55 [14] depth
A	7/8 - 14 UNF O-ring .67 [17] depth	7/16 - 20 UNF O-ring .50 [12,7] depth

**Note :** KPWR Blocks are installed directly on MLHP, MLHR and MLHH Motors with four screws 5/16-18UNC, 1.25 long ANSI B 18.3 or M8x35 - 8.8 DIN 912. Tightening torque 168±150 lb-in [1,7<sup>+0,2</sup> daNm].  
 KPWS Blocks are installed directly on MLHS Motors with two screws 3/8-16UNC, 1.25 long ANSI B 18.3 or M10x35 - 8.8 DIN 912. Tightening torque 336±310 lb-in [3,5<sup>+0,3</sup> daNm].



**SWITCH VALVE (continued)**

**SPECIFICATION DATA**

Parameters	Type	
	KPWT	KPWV
Flow Rate , GPM [lpm]	26.4 [100]	52.8 [200]
Rated Pressure , PSI [bar]	3625	[250]
Weight , lb	3.968	6.945
	[1,800]	[3,150]

**VALVE FOR MLHT HYDRAULIC MOTORS  
KPWT**

**VALVE FOR MLHV HYDRAULIC MOTORS  
KPWV**




	Thread Ports - P <sub>(A,B)</sub>	Thread Port - C
-	G3/4 .67 [17] depth	G1/4 .55 [14] depth
M	M27x2 .67 [17] depth	M14x1,5 .55 [14] depth
A	1 1/16-12 UN O-ring .67 [17] depth	7/16 - 20 UNF O-ring .50 [12,7] depth




	Thread Ports - P <sub>(A,B)</sub>	Thread Port - C
-	G 1 .79 [20] depth	G1/4 .55 [14] depth
M	M33x2 .79 [20] depth	M14x1,5 .55 [14] depth
A	1 5/16 - 12 UN O-ring .79 [20] depth	7/16 - 20 UNF O-ring .50 [12,7] depth

**Note :** KPWT Blocks are installed directly on MLHT Motors with four screws M10x40 - 8.8 DIN 912. Tightening torque 336±310 lb-in [3,5<sup>+0,3</sup> daNm].  
 KPWV Blocks are installed directly on MLHV Motors with four screws M12x45 - 8.8 DIN 912. Tightening torque 620±575 lb-in [6,5<sup>+0,5</sup> daNm].


**CROSSOVER RELIEF VALVES**



Single Crossover Relief Valve type KPE ...



Single Crossover Relief Valve type KPE ...



Dual Crossover Relief Valve type KPD ...


**SPECIFICATION DATA**

Parameters	Type			
	KPER	KPDR	KPES	KPDS
Flow Rate , GPM [lpm]	15.85 [60]			
Pressure Range* , PSI [bar]	435÷1450; [30 ÷ 100];	725÷3050; [50 ÷ 210];	1160÷4350 [80 ÷ 300]	
Weight , lb [kg]	3.42 [1,55]		3.31 [1,50]	

\*Pressure Settings are at flow rate of 1.32 GPM [5 lpm] and viscosity 150 SUS [32 mm<sup>2</sup>/s] (122° F [50 °C]).



**Rated Pressure**

- A → 1450 PSI [100 bar]
- B → 3050 PSI [210 bar]
- C → 3625 PSI [250 bar]




**VALVES FOR MLHP, MLHR, MLHH  
HYDRAULIC MOTORS**

**DUAL VALVE KPDR**





**SINGLE VALVE KPER**




**VALVES FOR MLHS  
HYDRAULIC MOTORS**

**DUAL VALVE KPDS**




**SINGLE VALVE KPES**




	Thread Ports - P <sub>(A,B)</sub>
-	G1/2 .79 [20] depth
M	M22x1,5 .79 [20] depth
A	7/8 - 14 UNF O-ring .79 [20] depth

**Note :** **KPDR** and **KPER** Blocks are installed directly on MLHP, MLHR and MLHH Motors with four screws M8x35 - 8.8 DIN 912 or 5/16-18 UNC, 1.5 long ANSI B 18.3 . Tightening torque 160 lb-in [1,8 daNm].  
**KPDS** and **KPES** Blocks are installed directly on MLHS Motors with two screws M10x35 - 8.8 DIN 912 or 3/8-16 UNC, 1.5 long ANSI B 18.3 . Tightening torque 310 lb-in [3,5 daNm].


**VALVES FOR MLHT HYDRAULIC MOTORS**



Single Crossover  
Relief Valve  
type KPEAT ...



Single Crossover  
Relief Valve  
type KPEBT ...



Dual Crossover  
Relief Valve  
type KPDT ...


**SPECIFICATION DATA**

Parameters	Type	
	KPE...T	KPDT
Flow Rate , GPM [lpm]	32 [120]	
Pressure Range* , PSI [bar]	1160÷3050 [80÷210]	
Weight , lb [kg]	11.24 [5,10]	12.21 [5,54]


\*Pressure Settings are at flow rate of 1.32 GPM [5 lpm] and viscosity 150 SUS [32 mm<sup>2</sup>/s] (122° F [50 °C]).

**Rated Pressure**

- A → 725 PSI [ 50 bar]
- B → 1450 PSI [100 bar]
- C → 2175 PSI [150 bar]
- D → 3045 PSI [210 bar]





**DUAL VALVE KPDT...**



**SINGLE VALVE KPEAT...**

**SINGLE VALVE KPEBT...**




Thread Ports - P <sub>(A,B)</sub>	
-	G3/4 .79 [20] depth
M	M27x2 .79 [20] depth
A	1 <sup>1</sup> / <sub>16</sub> -12 UN O-ring .79 [20] depth




**Note :** KPDT and KPE...T Blocks are installed directly on MT Motors with four screws M10x70 - 8.8 DIN 912. Tightening torque 310 lb-in [3,5 daNm].




**VALVES FOR MLHV HYDRAULIC MOTORS**



Single Crossover  
Relief Valve  
type KPEAV ...



Single Crossover  
Relief Valve  
type KPEBV ...




Dual Crossover  
Relief Valve  
type KPDRV ...

**SPECIFICATION DATA**


Parameters	Type		
	KPEAV	KPEBV	KPDRV
Flow Rate , GPM [lpm]	53 [200]		
Pressure Range* , PSI [bar]	145÷1450; 290÷3625 [10÷100]; [20÷250]		
Weight , lb	10.8	15.65	17.64
[kg]	[4,90]	[7,10]	[8,00]

\*Pressure Settings are at flow rate of 1.3 GPM [5 lpm] and viscosity 150 SUS [32 mm<sup>2</sup>/s] (122° F [50 °C]).

**Rated Pressure**




**DUAL VALVE KPDV**



**SINGLE VALVE KPEAV**


**SINGLE VALVE KPEBV**




	Thread Ports - P <sub>(A,B)</sub>
-	G1-A .79 [20] depth
M	M33x2 .79 [20] depth
A	1 5/16 -12 UN O-ring .79 [20] depth

**Note :** KPDV Blocks are installed directly on MLHV Motors with four screws M12x75 - 8.8 DIN 912.  
 KPEAV Blocks are installed directly on MLHV Motors with four screws M12x50 - 8.8 DIN 912.  
 KPEBV Blocks are installed directly on MLHV Motors with four screws M12x65 - 8.8 DIN 912.  
 Tightening torque 665 lb-in [7,5 daNm].


**VALVES FOR MLHRW and HW HYDRAULIC MOTORS**



Single Crossover  
Relief Valve  
type KPEAW ...



Single Crossover  
Relief Valve  
type KPEBW ...



Dual Crossover  
Relief Valve  
type KPDW ...


**SPECIFICATION DATA**

Parameters	Type	
	KPE...W	KPDW
Flow Rate , GPM [lpm]	15.85 [60]	
Pressure Range*, PSI [bar]	75÷580; [5 ÷ 40];	435÷1450; [30 ÷ 100]; 1160÷3625 [80 ÷ 250]
Weight , lb [kg]	3.97 [1,80]	6.39 [2,90]

\*Pressure Settings are at flow rate of 1.32 GPM [5 lpm]  
and viscosity 150 SUS [32 mm<sup>2</sup>/s] (122° F [50°C]).


**Rated Pressure**

- A → 1450 PSI [100 bar]
- B → 3050 PSI [210 bar]
- C → 3625 PSI [250 bar]




**VALVES FOR MLHRW and HW HYDRAULIC MOTORS**


**DUAL VALVE KPDW...**




**KPDW-...A**



**SINGLE VALVE KPEAW...**



**SINGLE VALVE KPEBW...**




	Thread Ports - P <sub>(A,B)</sub>	Thread Ports - D
-	G1/2 .63 [16] depth	G1/2 .47 [12] length
<b>M</b>	M22x1,5 .63 [16] depth	M22x1,5 .47 [12] length
<b>A</b>	7/8 - 14 UNF O-ring .63 [16] depth	.47 [12] UNF O-ring .51 [13] length

**Note :** KPDW and KPE..W Blocks assembly to MLHRW or HW motors is done with two screws (thread **D**) included in the valve set. Tightening torque 710 lb-in [8 daNm].

**CROSS PORT RELIEF VALVES**

**SPECIFICATION DATA**



Dual Cross Port Relief Valves type KPDHR... and KPDRK...

Parameters	Type					
	KPDHR			KPDRK		
Flow Rate, GPM [lpm]	15.85 [60]					
Pressure PSI	70÷580	435÷1450	1160÷3625	145÷580	435÷1450	1160÷3625
Range*, [bar]	[5÷40]	[30÷100]	[80÷250]	[10÷40]	[30÷100]	[80÷250]
Weight, lb	5.34			3.53		
[kg]	[2,420]			[1,600]		





\*Pressure Settings are at flow rate of 1.3 GPM [5 lpm] and viscosity 150 SUS [32 mm<sup>2</sup>/s] (122° F [50°C]).

**VALVES FOR HP AND HR HYDRAULIC MOTORS**

**DUAL VALVE KPDHR**

**VALVES FOR RK AND GHL HYDRAULIC MOTORS**

**DUAL VALVE KPDRK**



Thread Ports - P <sub>(A,B)</sub>	
-	G3/8
M	M18x1,5
A	3/4-16 UNF O-ring

Thread Ports - P <sub>(A,B)</sub>	
-	G1/2





## ORDER CODE - OVERCENTER VALVES WITH BRAKE CONTROL

1 2 3 4 5 6 7  
**K P B** [ ] - [ ] / [ ] / [ ] [ ] [ ] [ ] [ ]

### Pos.1 - Housing Type

- R** - Valve block for MP, MR and MH Motors
- S** - Valve block for MS Motors
- W** - Valve block for RW and HW Motors
- T** - Valve block for MT Motors
- V** - Valve block for MV Motors
- HR** - Valve block for HP and HR Motors

### Pos.2 - Pressure Range, PSI [bar]

- 250** - 1015÷3625 [70÷250], Std Setting 250 bar@5 lpm

### Pos.3 - Pilot Ratio

- 1** - 4,25:1

### Pos.4 - Number of Valves

- D** - Two Valves - Dual
- E** - One Valve - Single (for R and S only)
- AE** - One Valve on line A - Single (for T, V and W only)
- BE** - One Valve on line B - Single (for T, V and W only)

### Pos.5 - Threaded Ports

- omit - BSPP thread - ISO 228
- M** - Metric thread - ISO 262
- A** - Unified inch screw threads ANSI B 1.1 - 1982

### Pos.6 - Option [Paint]\*\*

- omit - no Paint
- P** - Painted
- PC** - Corrosion Protected Paint

### Pos.7 - Design Series

- omit - Factory specified

**Notes:** \* Color at customer's request.

## ORDER CODE - SWITCH VALVES

1 2 3 4  
**K P W** [ ] [ ] [ ] [ ]

### Pos.1 - Housing Type

- R** - Valve block for MP, MR and MH Motors
- S** - Valve block for MS Motors
- T** - Valve block for MT Motors
- V** - Valve block for MV Motors

### Pos.2 - Threaded Ports

- omit - BSPP thread - ISO 228
- M** - Metric thread - ISO 262
- A** - Unified inch screw threads ANSI B 1.1 - 1982

### Pos.3 - Option [Paint]\*\*

- omit - no Paint
- P** - Painted
- PC** - Corrosion Protected Paint

### Pos.4 - Design Series

- omit - Factory specified

**Notes:** \* Color at customer's request.

## ORDER CODE - CROSSOVER RELIEF VALVE

1 2 3 4 5 6  
**K P** [ ] [ ] [ ] / [ ] [ ] [ ] [ ]

### Pos.1 - Number of Valves

- D** - Two Valves - Dual
- E** - One Valve - Single (for R and S only)
- EA** - One Valve on line A - Single (for T, V and W only)
- EB** - One Valve on line B - Single (for T, V and W only)

### Pos.2 - Housing Type

- R** - Valve block for MP, MR and MH Motors
- S** - Valve block for MS Motors
- W** - Valve block for RW and HW Motors
- T** - Valve block for MT Motors
- V** - Valve block for MV Motors

### Pos.3 - Pressure Range, bar [PSI]

- 100\*** - 30÷100 [ 435÷1450], Std Setting 100 bar@5 lpm
- 210\*** - 50÷210 [ 725÷3050], Std Setting 210 bar@5 lpm
- 300\*** - 80÷300 [1160÷4350], Std Setting 250 bar@5 lpm
- 210\*\*** - 80÷210 [1160÷3050], Std Setting 210 bar@5 lpm
- 100\*\*\*** - 10÷100 [ 145÷1450], Std Setting 100 bar@5 lpm
- 250\*\*\*** - 20÷250 [ 290÷3625], Std Setting 250 bar@5 lpm

### Pos.4 - Threaded Ports

- omit - BSPP thread - ISO 228
- M** - Metric thread - ISO 262
- A** - Unified inch screw threads ANSI B 1.1 - 1982

### Pos.5 - Option [Paint]\*\*\*\*

- omit - no Paint
- P** - Painted
- PC** - Corrosion Protected Paint

### Pos.6 - Design Series

- omit - Factory specified

**Notes:** \* Useful for types R and S only.

\*\* Useful for types T only.

\*\*\* Useful for types V only.

\*\*\*\* Color at customer's request.

The Valve Blocks are mangano phosphatized as standard.

**ORDER CODE - CROSS PORT RELIEF VALVE**

	1	2	3	4	5	6
<b>K P</b>				/		

**Pos.1 - Number of Valves**

**D** - Two Valves - Dual

**Pos.2 - Housing Type**

**HR** - Valve block for HR Motors

**RK** - Valve block for RK and GHL Motors

**Pos.3 - Pressure Range, PSI [bar]**

**40** - 145÷ 580 [10÷ 40], Std Setting 100 bar@5 lpm

**100** - 435÷1450 [30÷100], Std Setting 100 bar@5 lpm

**250** - 1160÷3625 [80÷250], Std Setting 250 bar@5 lpm

**Pos.4 - Threaded Ports**

omit - BSPP thread - ISO 228

**M** - Metric thread - ISO 262

**A** - Unified inch screw threads ANSI B 1.1 - 1982

**Pos.5 - Option [Paint]\***

omit - no Paint

**P** - Painted

**PC** - Corrosion Protected Paint

**Pos.6 - Design Series**

omit - Factory specified

**Notes:** \* Color at customer's request.

The Valve Blocks are mangano phosphatized as standard.



# MOTOR-BRAKE SPECIAL FEATURES

---

Special Feature Description	Order Code	Motor type			
		B/HR	RWB	SW	TW
Low Leakage	LL	○	○	-	-
Low Speed Valving	LSV	○	○	-	-
Free Running	FR	-	-		-
Reverse Rotation	R	○	○	-	-
Paint*	P	○	○	○	○
Corrosion Protected Paint*	PC	○	○	○	○
Check Valves		-	○	S	S

\* color at customer's request.

- Optional
- Not applicable
- S Standard

# APPLICATION CALCULATION

## VEHICLE DRIVE CALCULATIONS

### 1. Motor speed: n, RPM

$$n = \frac{168 \times v_{mi} \times i}{R_m} \quad n = \frac{2,65 \times v_{km} \times i}{R_m}$$

$v_{km}$ - vehicle speed, km/h;

$v_{mi}$ - vehicle speed, mile/h;

$R_m$ - wheel rolling radius, m;

$R_{in}$ - wheel rolling radius, in;

$i$ - gear ratio between motor and wheels.

If no gearbox, use  $i=1$ .

### 2. Rolling resistance: RR, lbs [daN]

The resistance force resulted in wheels contact with different surfaces:

$$RR = G \times \rho$$

$G$ - total weight loaded on vehicle, lbs [daN];

$\rho$ - rolling resistance coefficient (Table 1).

Table 1

Rolling resistance coefficient In case of rubber tire rolling on different surfaces	
Surface	$\rho$
Concrete- faultless	0.010
Concrete- good	0.015
Concrete- bad	0.020
Asphalt- faultless	0.012
Asphalt- good	0.017
Asphalt- bad	0.022
Macadam- faultless	0.015
Macadam- good	0.022
Macadam- bad	0.037
Snow- 5 cm	0.025
Snow- 10 cm	0.037
Polluted covering- smooth	0.025
Polluted covering- sandy	0.040
Mud	0.037÷0.150
Sand- Gravel	0.060÷0.150
Sand- loose	0.160÷0.300

### 3. Grade resistance: GR, lbs [daN]

$$GR = G \times (\sin \alpha + \rho \times \cos \alpha)$$

$\alpha$ - gradient negotiation angle (Table 2)

Table 2

Grade %	$\alpha$ Degrees	Grade %	$\alpha$ Degrees
1%	0° 35'	12%	6° 5'
2%	1° 9'	15%	8° 31'
5%	2° 51'	20%	11° 19'
6%	3° 26'	25%	14° 3'
8%	4° 35'	32%	18°
10%	5° 43'	60%	31°

### 4. Acceleration force: FA, lbs [daN]

Force  $FA$  necessary for acceleration from 0 to maximum speed  $v$  and time  $t$  can be calculated with a formula:

$$FA = \frac{v_{mi} \times G}{22 \times t}, [\text{lbs}]; \quad FA = \frac{v_{km} \times G}{3,6 \times t}, [\text{daN}]$$

$FA$ - acceleration force, lbs [daN];

$t$ - time, [s].

### 5. Tractive effort: DP, lbs [daN]

Tractive effort  $DP$  is the additional force of trailer. This value will be established as follows:

-acc.to constructor's assessment;

-as calculating forces in items 2, 3 and 4 of trailer; the calculated sum corresponds to the tractive effort requested.

### 6. Total tractive effort: TE, lbs [daN]

Total tractive effort  $TE$  is total effort necessary for vehicle motion; that the sum of forces calculated in items from 2 to 5 and increased with 10 % because of air resistance.

$$TE = 1,1 \times (RR + GR + FA + DP)$$

$RR$ - force acquired to overcome the rolling resistance;

$GR$ - force acquired to slope upwards;

$FA$ - force acquired to accelerate (acceleration force);

$DP$ - additional tractive effort (trailer).

### 7. Motor Torque moment: M, lb-in [daNm]

Necessary torque moment for every hydraulic motor:

$$M = \frac{TE \times R_{in} [R_m]}{N \times i \times \eta_M}$$

$N$ - motor numbers;

$\eta_M$ - mechanical gear efficiency (if it is available).

### 8. Cohesion between tire and road covering: $M_w$ , lb-in [daNm]

$$M_w = \frac{G_w \times f \times R_{in} [R_m]}{i \times \eta_M}$$

To avoid wheel slipping, the following condition should be observed  $M_w > M$

$f$  - frictional factor;


$G_w$ - total weight over the wheels, lbs [daN].

Table 3

Surface	Frictional factor $f$
Steel on steel	0.15 ÷ 0.20
Rubber tire on polluted surface	0.5 ÷ 0.7
Rubber tire on asphalt	0.8 ÷ 1.0
Rubber tire on concrete	0.8 ÷ 1.0
Rubber tire on grass	0.4

**9.Radial motor loading:  $P_{rad}$ , lbs [daN]**

When motor is used for vehicle motion with wheels mounted directly on motor shaft, the total radial loading of motor shaft  $P_{rad}$  is a sum of motion force and weight force acting on one wheel.





- $G_w$  - Weight held by wheel;
- $P_{rad}$  - Total radial loading of motor shaft;
- $M/R$  - Motion force.

$$P_{rad} = \sqrt{G_w^2 + \left(\frac{M}{R}\right)^2}$$

In accordance with calculated loadings the suitable motor from the catalogue is selected.

**DRAINAGE SPACE AND DRAINAGE PRESSURE**

Advantages in oil drainage from drain space: Cleaning; Cooling and Seal lifetime prolonging.



# WARRANTY

M+S Hydraulic warrants, that its products, supplied directly to original equipment manufacturer, authorized distributor or other customer, will be free of defects in material or workmanship at the time of shipment from M+S Hydraulic and will conform to the products technical documentation (drawings and specifications) under sale agreement with Buyer.

This warranty will apply only to defects appearing within applicable Warranty period, mentioned below. If Buyer notifies M+S Hydraulic within the Warranty period about any such defects, M+S, at its sole option will replace or repair the defective products or their parts found by M+S Hydraulic to be defective in material or workmanship.

THE FOREGOING LIMITED WARRANTY IS AVAILABLE ONLY IF "M+S HYDRAULIC" IS PROMPTLY NOTIFIED IN WRITTEN OF THE ALLEGED DEFECT AND DOES NOT COVER FAILURE TO FUNCTION CAUSED BY DAMAGE TO THE PRODUCT, IMPROPER INSTALLATION, UNREASONABLE USE OR ABUSE OF THE PRODUCT, FAILURE TO PROVIDE OR USE OF IMPROPER MAINTENANCE OR USUAL, DEGRADATION OF THE PRODUCT DUE TO PHYSICAL ENVIRONMENTS OF AN USUAL NATURE. THE FOREGOING REMEDIES ARE THE SOLE AND EXCLUSIVE REMEDIES AVAILABLE TO CUSTOMER. To facilitate the inspection, M+S Hydraulic may require return of the product/part, which Buyer claims to be defective.

M+S Hydraulic shall not be liable for labor costs or any other expenses incurred during the disassembling or reinstalling of the product/part.

In case the claimed products are returned to M+S Hydraulic in bad condition: dirty, disassembled, with damaged or missing parts during transportation, the warranty will be considered as not applicable and the products will not be liable to repair.

## Warranty periods

**New products:** The Warranty period is limited to 24 consecutive months (2 years) from the date of production of the product.

**Repaired products:** If the product is repaired in M+S Hydraulic during its warranty period, the warranty period of the repaired item shall continue for the balance of original Warranty period or for a period equal to 50% of the original new product Warranty period, whichever is later.

**Spare parts:** The Warranty period for Spare parts is 12 consecutive months (1 year) from the dispatch date of such parts from M+S Hydraulic.

**LIMITATION OF LIABILITY** M+S Hydraulic's liability for claim of any kind, for loss or damage arising out of, connected with or resulting from an order, or from the performance or branch thereof, or from the design, manufacture, sale delivery, operation or use of any of its products shall be limited to, at M+S 's sole option, replacement, repair of any defective product or the issuance of a credit to Customer against any future purchases. Cash refunds will not be made under any circumstances and Customer will not be entitled to recover any damages of any kind against M+S Hydraulic, including but not limited to incidental or consequential damages, whether direct or indirect, known or unknown, foreseen or unforeseen.